

Connecting clamps with mounting base

Visually Detectable technopolymer

CLAMP

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 5005 blue colour, matte finish.
Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

SCREW AND NUT (SUPPLIED)

Cylindrical-head screws with hexagon socket in AISI 304 stainless steel with anti-seizure treatment.
Self-locking nut in AISI 304 stainless steel.

FEATURES AND APPLICATIONS

Clamps for tubes with a diameter of 18 ± 0.2 and 30 ± 0.2 mm.
For smaller diameter tubes, the hole reduction sleeve TCC-A can be used (ordered separately).
The "s" grub screw may be replaced by the kit TCC-KS.
The RAL 5005 blue colour is easily visible in case of accidental food contamination.
Particularly suitable for applications in the food and pharmaceutical industries.







TECHNICAL DATA

The resistance values shown in the table were measured during laboratory tests at ambient temperature with the screws tightened to the suggested torque "C#".

ELESA Original design

ACCESSORIES ON REQUEST (TO BE ORDERED SEPARATELY)

- TCC-A: reduction sleeves.
- TCC-KS: clamping kit.
- TCC-KV: screws and clamping nuts.
- GN 990: connecting tubes.



STAINLESS STEEL

Code	Description	d	L	H	d ₂	f ±0.2	h ₁	h ₂	l ₁	l ₂	l ₃	s	C# [Nm]	F1* [N]	M1** [Nm]	⚖️
191111	TCC-AB-18-VD	18	45	34	5.3	30	5	25	26	36.5	20	M6	5	1050	8	29
191211	TCC-AB-30-VD	30	60	50	6.5	40	8	40	42	53.5	27	M8	12	1650	33	75

Suggested torque for screw assembly.

* Resistance to tube pull out

** Resistance to tube rotation