

# INSERTI FILETTATI CILINDRICI GODRONATI

## KNURLED CYLINDRICAL THREADED INSERTS

### BLINDNIETMUTTERN RUNDSCHAFT GERÄNDELT

### INSERTS FILETÉS CRANTÉS CYLINDRIQUES

### TUERCAS REMACHABLES CILINDRICAS ESTRIADAS

ACCIAIO Z. B. CROMO III  
STEEL ZINC PLATED Cr III  
STAHL VERZINKT Cr III  
ACIER ZINGUÉ Cr III  
ACERO CINCADO Cr III


ZIGRINATO SOTTO LA TESTA  
KNURLED UNDERNEATH THE HEAD

# 2

| CODICE<br>CODE                                                       |  | S<br>GRIP                                        | D<br>+0,07/-0,1              |  | T<br>+/-0,5          | K<br>+/-0,15             | L<br>+/-0,5            | I<br>~                       |  | Nm |
|----------------------------------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------------------------|------------------------------|-----------------------------------------------------------------------------------|----------------------|--------------------------|------------------------|------------------------------|-----------------------------------------------------------------------------------|----|
| 85ACITTGM03C<br>85ACITTGM03L                                         | M3                                                                                | 0,5 - 1,5<br>1,5 - 3,0                           | 4,9                          | 5                                                                                 | 8<br>7               | 0,8                      | 10<br>11,5             | 6<br>8                       | 2                                                                                 |    |
| 85ACITTGM04C<br>85ACITTGM04L                                         | M4                                                                                | 0,5 - 2,0<br>2,0 - 3,5                           | 5,9                          | 6                                                                                 | 9                    | 0,8                      | 10,5<br>12             | 6<br>6                       | 5                                                                                 |    |
| 85ACITTGM05C<br>85ACITTGM05L                                         | M5                                                                                | 0,5 - 2,5<br>2,5 - 5,0                           | 6,9                          | 7                                                                                 | 10<br>10             | 1<br>1                   | 13<br>16,5             | 7,5<br>8,5                   | 8,5                                                                               |    |
| 85ACITTGM06C<br>85ACITTGM06L                                         | M6                                                                                | 0,5 - 3,0<br>3,0 - 5,5                           | 8,9                          | 9                                                                                 | 12,3<br>12,3         | 1,3<br>1,3               | 15<br>19,5             | 9,2<br>10,5                  | 15                                                                                |    |
| 85ACITTGM08C<br>85ACITTGM08L                                         | M8                                                                                | 1,0 - 3,5<br>3,5 - 6,0                           | 10,9                         | 11                                                                                | 14,5<br>14,5         | 1,5<br>1,5               | 18,5<br>21             | 11,5                         | 26                                                                                |    |
| 85ACITTGM10C12<br>85ACITTGM10L12<br>85ACITTGM10C13<br>85ACITTGM10L13 | M10                                                                               | 1,0 - 3,5<br>3,0 - 6,0<br>1,0 - 4,0<br>4,0 - 6,5 | 11,9<br>11,9<br>12,9<br>12,9 | 12<br>12<br>13<br>13                                                              | 16<br>16<br>17<br>17 | 1,7<br>1,6<br>1,7<br>1,7 | 19<br>24<br>21,5<br>24 | 12,5<br>18,5<br>13,5<br>13,5 | 50                                                                                |    |
| 85ACITTGM12C15<br>85ACITTGM12L15<br>85ACITTGM12C16<br>85ACITTGM12L16 | M12                                                                               | 1,0 - 4,0<br>4,0 - 6,5<br>1,0 - 3,5<br>3,5 - 6,0 | 14,9<br>14,9<br>15,9<br>15,9 | 15<br>15<br>16<br>16                                                              | 18<br>18<br>22<br>22 | 1,7<br>1,7<br>2<br>2     | 22<br>25<br>25<br>28   | 13,5<br>14<br>15<br>16,5     | 80                                                                                |    |

## ITTG


**TESTA TONDA**  
FLAT HEAD  
FLACHKOPF  
TÊTE CYLINDRIQUE  
CABEZA PLANA



| CODICE<br>CODE                                                       |  | S<br>GRIP                                        | D<br>+0,07/-0,1              |  | T<br>+/-0,5           | K*<br>+/-0,15            | L<br>+/-0,5              | I<br>~                   |  | Nm |
|----------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------|------------------------------|-------------------------------------------------------------------------------------|-----------------------|--------------------------|--------------------------|--------------------------|-------------------------------------------------------------------------------------|----|
| 85ACITRGM03C<br>85ACITRGM03L                                         | M3                                                                                  | 0,5 - 2,0<br>2,0 - 3,5                           | 4,9                          | 5                                                                                   | 6                     | 0,5                      | 9<br>11,5                | 6,5<br>5,5               | 1                                                                                   |    |
| 85ACITRGM04C<br>85ACITRGM04L                                         | M4                                                                                  | 0,5 - 2,0<br>2,0 - 4,0                           | 5,9                          | 6                                                                                   | 7<br>7                | 0,5                      | 11,2<br>13               | 7<br>7                   | 3                                                                                   |    |
| 85ACITRGM05C<br>85ACITRGM05L                                         | M5                                                                                  | 0,5 - 2,5<br>2,0 - 4,0                           | 6,9                          | 7                                                                                   | 8                     | 0,5<br>0,5               | 11,5<br>13               | 7<br>7                   | 6                                                                                   |    |
| 85ACITRGM06C<br>85ACITRGM06L<br>85ACITRGM06LV                        | M6                                                                                  | 0,5 - 2,5<br>2,5 - 4,5<br>3,5 - 6,0              | 8,9                          | 9                                                                                   | 10                    | 0,6                      | 14<br>16<br>18           | 8,5<br>10,5<br>12,5      | 11                                                                                  |    |
| 85ACITRGM08C<br>85ACITRGM08L                                         | M8                                                                                  | 1,0 - 3,0<br>3,0 - 5,0                           | 10,9                         | 11                                                                                  | 12<br>12              | 0,65                     | 16,5<br>18,5             | 10<br>10                 | 20                                                                                  |    |
| 85ACITRGM10C12<br>85ACITRGM10L12<br>85ACITRGM10C13<br>85ACITRGM10L13 | M10                                                                                 | 1,0 - 3,5<br>3,5 - 5,5<br>1,0 - 3,5<br>3,5 - 6,0 | 11,9<br>11,9<br>12,9<br>12,9 | 12<br>12<br>13<br>13                                                                | 13<br>13<br>14<br>14  | 0,7<br>0,7<br>0,7<br>0,7 | 19,5<br>22<br>19,5<br>22 | 13<br>17<br>12,5<br>12,5 | 32                                                                                  |    |
| 85ACITRGM12C15<br>85ACITRGM12C16<br>85ACITRGM12L16                   | M12                                                                                 | 0,5 - 3,5<br>1,0 - 4,0<br>4,0 - 6,0              | 14,9<br>15,9<br>15,9         | 15<br>16<br>16                                                                      | 16,5<br>17,6<br>17,15 | 0,85<br>0,75<br>0,6      | 22,5<br>24,2<br>27       | 16<br>16<br>16           | 50                                                                                  |    |

## ITRG

**TESTA RIDOTTA**  
REDUCED COUNTERSUNK HEAD  
KLEINER SENKKOPF  
TÊTE RÉDUITE  
CABEZA REDUCIDA



\* K dopo la posa  
K after setting