

2

ACCIAIO INOX  
STAINLESS STEEL  
EDELSTAHL  
ACIER INOX  
INOX

A4

**INSERTI FILETTATI SEMIESAGONALI**  
SEMI-HEXAGONAL THREADED INSERTS  
BLINDNIETMUTTERN TEILSECHSKANT  
INSERTS FILETÉS SEMI-HEXAGONAUX  
TUERCAS REMACHABLES SEMI-HEXAGONALES

# ITTSE


## TESTA TONDA

FLAT HEAD

FLACHKOPF

TÊTE CYLINDRIQUE

CABEZA PLANA



| CODICE<br>CODE    |  | S<br>GRIP | M<br><small>+0,07/-0,1</small> | M1<br><small>0,1/-0</small> | T<br><small>+/-0,5</small> | K<br><small>+/-0,15</small> | L<br><small>+/-0,5</small> | I<br><small>~</small> | <br>Nm |
|-------------------|-----------------------------------------------------------------------------------|-----------|--------------------------------|-----------------------------|----------------------------|-----------------------------|----------------------------|-----------------------|-------------------------------------------------------------------------------------------|
| 85IXA4ITTSEM03C   | M3                                                                                | 0,5 - 1,5 | 4,9                            | 5                           | 8                          | 0,8                         | 9                          | 6                     | 2                                                                                         |
| 85IXA4ITTSEM04C   | M4                                                                                | 0,5 - 2,0 | 5,9                            | 6                           | 9                          | 0,8                         | 11                         | 7,2                   | 5                                                                                         |
| 85IXA4ITTSEM05C   | M5                                                                                | 0,5 - 2,5 | 6,9                            | 7                           | 10                         | 1                           | 12                         | 7,5                   | 8,5                                                                                       |
| 85IXA4ITTSEM06C   | M6                                                                                | 0,5 - 3,0 | 8,9                            | 9                           | 12,7                       | 1,3                         | 15,5                       | 9                     | 15                                                                                        |
| 85IXA4ITTSEM08C   | M8                                                                                | 1,0 - 3,5 | 10,9                           | 11                          | 16                         | 1,5                         | 18                         | 10                    | 26                                                                                        |
| 85IXA4ITTSEM10C13 | M10                                                                               | 1,0 - 4,0 | 12,9                           | 13                          | 18                         | 1,7                         | 21                         | 16                    | 50                                                                                        |
| 85IXA4ITTSEM12C16 | M12                                                                               | 1,0 - 4,0 | 15,9                           | 16                          | 23                         | 2                           | 28                         | 18                    | 80                                                                                        |

# IERSE


## TESTA RIDOTTA

REDUCED COUNTERSUNK HEAD

KLEINER SENKKOPF

TÊTE RÉDUITE

CABEZA REDUCIDA



\* K dopo la posa  
K after setting

| CODICE<br>CODE    |  | S<br>GRIP | M<br><small>+0,07/-0,1</small> | M1<br><small>0,1/-0</small> | T<br><small>+/-0,5</small> | K*<br><small>+/-0,15</small> | L<br><small>+/-0,5</small> | I<br><small>~</small> | <br>Nm |
|-------------------|-------------------------------------------------------------------------------------|-----------|--------------------------------|-----------------------------|----------------------------|------------------------------|----------------------------|-----------------------|---------------------------------------------------------------------------------------------|
| 85IXA4IERSEM03C   | M3                                                                                  | 0,5 - 1,5 | 4,9                            | 5                           | 6                          | 0,5                          | 9                          | 6                     | 1                                                                                           |
| 85IXA4IERSEM04C   | M4                                                                                  | 0,5 - 2,0 | 5,9                            | 6                           | 7                          | 0,5                          | 12                         | 7,5                   | 3                                                                                           |
| 85IXA4IERSEM05C   | M5                                                                                  | 0,5 - 2,5 | 6,9                            | 7                           | 8                          | 0,6                          | 13                         | 8                     | 6                                                                                           |
| 85IXA4IERSEM06C   | M6                                                                                  | 1,0 - 3,0 | 8,9                            | 9                           | 10                         | 0,6                          | 16                         | 9,2                   | 11                                                                                          |
| 85IXA4IERSEM08C   | M8                                                                                  | 1,0 - 3,5 | 10,9                           | 11                          | 12                         | 0,65                         | 17,5                       | 10                    | 20                                                                                          |
| 85IXA4IERSEM10C13 | M10                                                                                 | 1,0 - 4,0 | 12,9                           | 13                          | 14,5                       | 0,75                         | 21                         | 14                    | 32                                                                                          |
| 85IXA4IERSEM12C16 | M12                                                                                 | 1,0 - 4,0 | 15,9                           | 16                          | 17,5                       | 0,8                          | 24                         | 18                    | 50                                                                                          |